NSG 4070C APPLICATION FOR MIL-STD 461G CS 114

Test parameter

| MIL-STD 461G CS 114 |
|--|
| 4 kHz to 200 MHz |
| see diagrams |
| 1 kHz pulse modulation, 50 % duty cycle |
| Measuring deviation max. 3 dB |
| Substitution method with 6 dB current limitation |
| Required for limiting the induced current |
| |


Equipment

| Signal generation: | NSG 4070C-60 |
|--------------------------|-----------------------------------|
| Modulator: | included in NSG 4070C-60 |
| Power meter: | 5x included in NSG 4070C-60 |
| Power amplifier: | included in NSG 4070C-60 |
| Directional coupler: | included in NSG 4070C-60 |
| Current injection probe: | CIP 9136A |
| Monitoring probe: | MD 4070A |
| Calibration jig: | 2x PCJ 9201B |
| Termination: | 2x 50 Ω 10 W |
| Attenuation: | 3 dB, 6 dB, 10 dB, 20 dB as |
| | shown in table 1 |
| Device control: | incl. in NSG 4070 user interface |
| Software (optional): | icd.control version 6.1 or higher |



WARNING: The power meter inputs are very sensitive. It is the user's responsibility to ensure that the selected test levels does not damage the equipment. Any hardware/setup changes should be calculated before starting the test.

Calibration set-up for monitoring probe



Remarks:


It is recommended to connect the MD 4070 remote port with the user port of NSG 4070 and select the function "MD 4070 adaptive probe" in the NSG 4070 firmware (version 2.23 or higher). The monitoring probe MD 4070 will be calibrated in passive and active mode automatically.






1


Test level — for MIL STD 461G CS114 curve #1




Test level — for MIL STD 461G CS114 curve #2




Test level — for MIL STD 461G CS114 curve #3



Test level — for MIL STD 461G CS114 curve #4



Test level — for MIL STD 461G CS114 curve #5




Use of the attenuators on the BCI probe and on the power meter channel 1 of NSG 4070C-60 $\,$

| Test level of MIL-STD-461G CS114 | Attenuator in dB on BCI probe CIP 9136A | Attenuator in dB on power meter 1 of NSG 4070C-60 |
|-------------------------------------|---|---|
| Curve #1 | 33 | 0 |
| Curve #2 | 26 | 0 |
| Curve #3 | 20 | 0 |
| Curve #4 | 13 | 0 |
| Curve #5 | 0 | 20 |
| 77 dBµA (4 kHz to 10 kHz) | 0 | 0 |
| 77 dBµA (10 kHz to 1 MHz) | 33 | 0 |

Table 1: Use of the attenuators




Calibration set-up for curve #1 to curve #4 and 77 dBµA (for 77 dBµA in the range 10 kHz to 1 MHz)




Please use the attenuator with values as given in Table 1 to allow level setting above the amplifier noise.

Verification set-up for curve #1 to curve #4 and 77 dBµA (for 77 dBµA in the range 10 kHz to 1 MHz)



Please use the same attenuators and the same cables as used for system and probe calibration.


Test set-up for curve #1 to curve #4 and 77 dBµA (for 77 dBµA in the range 10 kHz to 1 MHz)



Please use the same attenuators and the same cables as used for system and probe calibration.




Calibration set-up for curve #5




Please use a 20 dB attenuator to protect power meter channel 1. Remove the attenuator on the BCI probe.

Verification set-up for curve #5



Please use the same cables as used for system and probe calibration.


Test set-up for curve #5



Please use the same cables as used for system and probe calibration.




Calibration set-up for 77 dBµA in the range 4 kHz to 10 kHz



Please remove the 20 dB attenuator to protect power meter and the attenuator on the BCI probe.

Test set-up for for 77 dBµA in the range 4 kHz to 10 kHz



Please use the same cables as used for system and probe calibration.

AMETEK CTS Europe GmbH

Landsberger Str. 255 \cdot 12623 Berlin \cdot Germany T +49 30 56 59 88 35 F +49 30 56 59 88 34 info.rf.cts@ametek.com **www.ametek-cts.com**

© December 2017 Teseq®

Specifications subject to change without notice. Teseq® is an ISO-registered company. Its products are designed and manufactured under the strict quality and environmental requirements of the ISO 9001. This document has been carefully checked. However, Teseq® does not assume any liability for errors or inaccuracies.

83-257510 E01 MIL-STD 461G Dec. 2017



